














# Standard Tube Sets / Tubing Assemblies













Standard tube sets for your application ■ Ready to use ■ Usually available from stock

Platinum-cured silicone tubing ■ Single- or double packed ■ Gammairradiated ■ With pharmaconform certification

Manufactured in cleanroom (ISO Class 8) in conformity to ISO 9001-2008 and ISO 13485-2003

Customized tubesets on request

Drawing	Connections	Tubing (-length)	Packaging	Product Code
	a. Luer-female b. MPC-female	I-SA P60 48-16-80 Length: 50cm with clamp	Single	TS1A19h-50
	a. Luer-male b. MPC-female	I-SA P60 48-16-80 Length: 60cm with clamp	Single	TS1A20g-60
	a. open tubing b. MPC-female	I-SA P60 48-16-80 Length: 60cm with clamp	Single	TS1A0
	a. open tubing b. MPC-female	I-SA P60 95-32-159 Length: 75cm with clamp	Single	TS2H0-75
	a. open tubing b. MPC-male	I-SA P60 48-16-80 Length: 60cm with clamp	Single	TS3A0
	a. MPC-female b. MPC-female	I-SA P60 95-24-143 Length: 3cm	Single	TS02B2
	a. MPC-female b. MPC-female	I-SA P60 95-24-143 Length: 25cm	Double	TS2B2
	a. MPC-male b. MPC-male	I-SA P60 95-24-143 Length: 25cm	Double	TS4B4
	a. MPC-male b. MPC-female	I-SA P60 95-32-159 Length: 50cm with clamp	Single	TS2H4-50
	a. MPCK-female b. MPC-male	I-SA P60 95-32-159 Length: 100cm with clamp	Double	TS-95-10-CFCM
	a. MPCK-female b. MPC-male	I-SA P60 95-32-159 Length: 200cm with clamp	Double	TS-95-20-CFCM
	a. MPCK-female b. MPCK-female	I-SA P60 95-32-159 Length: 100cm with clamp	Double	TS-95-10-CFCF
	a. Mini-TC25 (3/4") b. MPCK-female incl. TC-Gasket (3/4")	I-SA P60 95-32-159 Length: 100cm with clamp	Double	TS-95-10-CFTC25

Drawing	Connections	Tubing (-length)	Packaging	Product Code
	a. MPC-male b. MPCK-female b. MPCK-female	I-SA P60 95-32-159 Length: 3 x 15cm with clamps	Double	TS-95-015-CM2CF
	a. MPCK-female b. MPCK-female b. MPCK-female	I-SA P60 95-32-159 Length: 3 x 20cm with clamps	Double	TS-95-02-2CFCF
	a. MPC-female b. MPX-female	I-SA P60 127-24-175 I-SA P60 95-24-143 Total Length: 30cm with clamp	Double	TS2BaC5
	a. MPXK-female b. MPX-male	I-SA P60 127-32-191 Length: 100cm with clamp	Double	TS-127-10-XFXM
	a. MPXK-female b. MPX-male	I-SA P60 127-32-191 Length: 200cm with clamp	Double	TS-127-20-XFXM
	a. MPXK-female b. MPXK-female	I-SA P60 127-32-191 Length: 100cm with clamp	Double	TS-127-10-XFXF
	a. MPXK-female b. MPXK-female	I-SA P60 127-32-191 Length: 200cm with clamp	Double	TS-127-20-XFXF
	a. TC50 (1-1/2") b. MPXK-female incl. TC-Gasket(1-1/2")	I-SA P60 127-32-191 Length: 100cm with clamp	Double	TS-127-10-XFTC50
	a. TC50 (1-1/2") b. MPX-male incl. TC-Gasket(1-1/2")	I-SA P60 127-32-191 Length: 100cm with clamp	Double	TS-127-10-TC50XM
	a. TC50 (1-1/2") b. TC50 (1-1/2") incl. TC-Gasket(1-1/2")	I-SA P60 127-32-191 Length: 150cm with clamp	Double	TS-127-15-TC50TC50
	a. MPX-male b. MPXK-female c. MPXK-female	I-SA P60 127-32-191 Length: 3 x 20cm with clamps	Double	TS-127-02-XM2XF
	a. MPXK-female b. MPX-male c. MPX-male	I-SA P60 127-32-191 Length: 3 x 20cm with clamps	Double	TS-127-02-XF2XM